

Type: Female connector straight with 2 rows

Termination: Press-fit, solder, THTR

Number of contacts: 32, 48, 64, 96

Pitch: 2.54 mm


Operational current: 1.5 A

Packaging: Tube

Standard: IEC 60603-2



Technical Specifications on page 36



Accessories

- Processing tools p. 300
- Coding p. 132
- Shroud p. 123

Similar products

- Type C with switching function see on p. 124
- VMEx see on p. 120
- Type C in IDC see on p. 128






Mating connector / Application:

Type C Male connector (p. 52)

Type R Male connector (p. 74)



Press-fit - Performance level II






No. of contacts	Contact arrangement	PCB thickness	Termination length L 			
			3.2 mm	4.6 mm	13 mm	17 mm
			Part number			
32		1.5 - 2.0 mm	104-60014-01	-	104-65015-01	104-65016-01
		2.0 - 2.8 mm	-	104-60014-02	104-65015-02	104-65016-02
		> 2.8 mm	-	104-60014-03	104-65015-03	104-65016-03
48		1.5 - 2.0 mm	104-60044-01	-	104-65045-01	104-65046-01
		2.0 - 2.8 mm	-	104-60044-02	104-65045-02	104-65046-02
		> 2.8 mm	-	104-60044-03	104-65045-03	104-65046-03
64		> 1.5 mm	-	304-60054-02	304-65055-03	304-65056-04
96		> 1.5 mm	-	304-60064-02	304-65065-03	304-65066-04

On request

- contact arrangement
- without flange
- performance level I + III or customized
- special contact length
- alternative contact surface
Sn e. g. for WireWrap
- PCB hole 0,85 mm see on p. 37



Solder - Performance level II




No. of contacts	Contact arrangement	Termination length L 				
		2.5 mm	3.4 mm	4.6 mm	13 mm	Solder lug
		Part number				
32		104-40014	-	-	104-40016	-
48		104-40044	-	-	104-40046	-
64		304-40054-05	304-40054-01	304-40054-02	304-40055-03	104-40115
96		304-40064-05	304-40064-01	304-40064-02	304-40065-03	104-40075

On request

- contact arrangement
- Board-Lock p. 131
- performance level I + III or customized
- special contact length



THTR - Performance level II

No. of contacts	Contact arrangement	Termination length L 		
		2.5 mm	3.4 mm	4.6 mm
		Part number		
64		304-40054-05TH	304-40054-01TH	304-40054-02TH
96		304-40064-05TH	304-40064-01TH	304-40064-02TH