DATA SHEET





70-degree bent nose for maximum work visibility in confined areas. Knurled jaws for sure wrapping and looping. Curved handles provide greater tool control.

Specifications

Overall Length:	6.375" (161.9 mm)	Jaw Length:	1.5" (38.1 mm)
Jaw Width:	0.688" (17.5 mm)	Jaw Thickness:	3/8" (9.5 mm)
Jaw Capacity:	1.28" (32.5 mm)	Point Diameter:	3/32" (2.38 mm)
Handle Colour:	Yellow	Handle Finish:	Plastic dipped
Weight:	0.30 lb (0.14 kg)		