

## Profile Shallow Wide Surface 30

Profile Shallow Wide Surface 30 CDE-9/T 3m anodised  
0022609



### Product features

- A shallow wide 1000mm length anodised aluminium lighting profile that can be combined with multiple click diffusers (flat opal - 0022624, round frosted - 0022625, square opal - 0022633) with a maximum LED strip width of 20mm. Can be mounted with 'Profile HO surface 16 raw alu.' or dedicated plates. Additional accessories like end caps, profile holders or mounting brackets need to be ordered separately.



## PRODUCT OVERVIEW

Product name	Profile Shallow Wide Surface 30 CDE-9/T 3m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278031
Warranty	3 years
Housing colour	Silver
Product EAN number	5410288226095

## DATA TABLE

### General data

Product name	Profile Shallow Wide Surface 30 CDE-9/T 3m anodised
Technology	Accessory
Housing	Aluminium
General application	Retail
ETIM Class	EC002557
E-number FI	4278031
Warranty	3 years

### Physical data

Housing colour	Silver
Nominal Product Length (mm)	3000
Nominal Product Width (mm)	33.4
Nominal Product Height (mm)	12.8
Weight (kg)	1.1

### Packaging

Single packaging type	Carton
Product EAN number	5410288226095
Packaging single length / height (cm)	300.0

## Profile Shallow Wide Surface 30

*Profile Shallow Wide Surface 30 CDE-9/T 3m anodised*

0022609

Packaging single width (cm)	3.0
Packaging single depth (cm)	2.0
DUN14 (outer)	05410288226095
Units per outer package	50
Packaging outer length / height (cm)	305.0
Packaging outer width (cm)	16.0
Packaging outer depth (cm)	16.0

### TECHNICAL DRAWINGS

