

## Inverto Pendant

*Inverto Pend Rmt WW 1-10v Silver*  
3080127



### Product features

- Pendant luminaire with remote driver, wire to base with pluggable connection for easy installation, suitable for looping, switchable driver, silver coloured aluminium housing, 1,566lm, 16W, 98lm/W, 3000K, 350mA, CRI:80, 40° beam Angle, 1-10V dimmable, IP20, IK07, lifespan: 60,000hrs (L80:B20), 18.50x29.6x11.5mm.



## PRODUCT OVERVIEW

Product name	Inverto Pend Rmt WW 1-10v Silver
Technology	LED
Housing	Aluminium
Mount	Pendant surface
Environment	Internal
General application	Hospitality
ETIM Class	EC001743
Warranty	5 years
Fixture luminous flux (lm)	1566
Luminaire efficacy (lm/W)	98
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Consistency (SDCM)	3
Beam Angle (°)	40
Photobiological Risk Group	RG1
Total power consumption (W)	16
Electrical protection	Class II
Control gear type	Electronic ballast
Dimmable	Yes
Dimming method	1-10V (Analogue)
Minimum dimming level (%)	5
Housing colour	RAL 9022 - Pearl light grey
IP rating	IP20
IK rating	IK07
Product EAN number	8711971801276

## DATA TABLE

General data

## Inverto Pendant

*Inverto Pend Rmt WW 1-10v Silver*  
3080127

Product name	Inverto Pend Rmt WW 1-10v Silver
Technology	LED
Housing	Aluminium
Mount	Pendant surface
Environment	Internal
General application	Hospitality
Operating temperature range (°C)	-25°C...+25°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001743
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	1566
Luminaire efficacy (lm/W)	98
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Beam Angle (°)	40
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	16
Mains voltage (V)	220-240V
Electrical protection	Class II
Control gear type	Electronic ballast
Transformer required	Yes
Dimmable	Yes
Dimming method	1-10V (Analogue)
Minimum dimming level (%)	5
Drive current (mA)	350
Inrush Current (A)	45
Inrush Duration (µs)	20
Energy Efficiency Class (A->G) of contained light source	D
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	50
Max. Luminaires per 16A C Breaker	80

### Lifetime data

Lifespan L70 B50	60000
Lifespan L80 B20	60000
Lifespan L90 B10	56100

### Physical data

Housing colour	RAL 9022 - Pearl light grey
IP rating	IP20

## Inverto Pendant

*Inverto Pend Rmt WW 1-10v Silver*

3080127

IK rating	IK07
Diffuser finish	Transparent
Diffuser material	Glass
Nominal Product Length (mm)	110
Nominal Product Width (mm)	110
Nominal Product Height (mm)	110
Weight (kg)	1.429

### Packaging

Single packaging type	Carton
Product EAN number	8711971801276
Packaging single length / height (cm)	18.5
Packaging single width (cm)	29.6
Packaging single depth (cm)	11.5
DUN14 (outer)	08711971801276
Units per outer package	1
Packaging outer length / height (cm)	18.5
Packaging outer width (cm)	29.6
Packaging outer depth (cm)	11.5

### Safety data

Optimal operating condition (°C)	-25-25
----------------------------------	--------

## PHOTOMETRY

## TECHNICAL DRAWINGS

