

Nuts

For T-grooves




Application:

For clamping in T-grooves.

Version:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form

Art. no.	26195 110
Type	standard
Nominal dimension of groove	28 mm
Slot nut width	27.7 mm
Thread dimension	M24
Length	44 mm
Height	36 mm
Slot nut height	18 mm
DIN	508



EAN-Code

4020772080105