


- NOTES:**
- MATERIALS:**
 HOOD: PBT GF UL94 V-0 BLACK
 FRONTSEALING: SILICONE VMQ BLUE
 SCREW: STAINLESS STEEL
 O-RING: NBR BLACK
 - TEMPERATURE RANGE: -30°C TO +90°C
 - RECOMMENDED TORQUE FOR SCREW:
 35Ncm (3.1 in.LB)
 MAX. TORQUE: 68Ncm (6 in.LB)
 - SINGLE PACKED

(1 : 1)



* COMPLETELY TIGHTENED

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance ± 0,3 unless otherw. specified		scale: 1,5:1 (1:1)
				date	name	material: SEE TABLE
				drawn 07.02.2014	Heinrich	title: WATER RESISTANT D-SUB HOOD
				appd. 07.02.2014	Huether	(b) 9 pos. with short screw 4-40UNC thread/ stainless steel
				norm	d-old	dwg no:
b	Ä5061	07.02.2014	Heinrich			DIN-A3
a	Origin					15K1A1153
rev.	description	date	name	part no:		(b) 15-004710

sh: 1