



Part Number : [192000025](#)

Product Description : Avikrimp Seamless Butt Splice for 18-22 AWG Wire, Super Duty

Series Number : 19200

Status : Active

Product Category : Splices

Engineering Number : AS-845 PINK



Documents & Resources

Drawings

[Drawing 192000025_sd.pdf](#)


Specifications

[Product Specification PS-19902-013-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2021)4569-DC (8 July 2021)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Splices
Series	19200
Description	Avikrimp Seamless Butt Splice for 18-22 AWG Wire, Super Duty
Comments	Pink
Product Family	Splices
Product Name	Avikrimp
UPC	800756877891

Agency

UL	E32244
----	--------

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Pink
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.573/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	3.50mm

Wire Size (AWG)	18, 20, 22
-----------------	------------

This document was generated on Sep 26, 2023