

FEATURES

- Pins made from true thermocouple alloys
- ANSI colour coding for quick and easy identification
- Polarized flat pin contacts for an accurate connection
- Made from rugged glass-filled thermoplastic
- Able to withstand a high temperature of 220°C
- For use with stranded or solid wires
- Accepts thermocouple cable up to 4mm in diameter

RS PRO ANSI Thermocouple Connector for use with Type K Thermocouple Type K, Miniature

RS Stock No.: 769-1101



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS PRO a miniature in-line thermocouple plug connector which is colour coded in accordance with ANSI specification. This thermocouple plug is ideal for connecting your thermocouple probe or wire terminals to extension or compensating cables. This male plug also provides a quick, safe and error-free way of replacing your existing thermocouples. The plug housing is made from a rugged glass-filled thermoplastic which is impact resistant and able to withstand high temperatures of up to 220°C. The pins on this male connector have a flat design and are polarised to ensure an accurate connection. The housing is ANSI colour coded with the thermocouple type clearly indicated on the front for easy identification.

Accessories

A cable clamp and rubber grommet are available for use with these miniature thermocouple connectors

Stock number <u>236-4104</u> – cable clamp

Stock number <u>666-7365</u> – rubber grommet

General Specifications

| Accessory Type | Thermocouple Connector |
|-------------------------------|---------------------------------------|
| For Use With | Type K Thermocouple |
| Thermocouple Type | K |
| Maximum Temperature | 220°C |
| Positive Contact (Alloy Type) | Nickel Chromium |
| Negative Contact (Alloy Type) | Nickel Alloy |
| Clamp Type | Simple captive screw clamp connection |
| Number of Ways | 12 |
| Colour | Yellow |
| Applications | Miniature In-Line Connector |



| Connector Type | Thermocouple Connector | | |
|-----------------------------|------------------------|--|--|
| Thermocouple Cable Diameter | 4mm | | |

Operation Environment Specifications

| | 7 |
|------------------------------|-------|
| Maximum Continuous Operating | 22000 |
| Temperature | 220°C |

Approvals

| Compliance/Certifications | RoHS |
|---------------------------|------|
|---------------------------|------|





Accessories

 Cable clamp for miniature connectors – Allied code 70641746

Allied code 70641746 RS order number **236-4104**




· Rubber grommet for miniature connectors -

Allied code 70646835

RS order number 666-7365 (25 per pack)







Miniature in-line Plug


(dimensions in mm)

ORDERING INFORMATION

| MODEL | Allied Code | RS ORDER NUMBER |
|--|--------------------|-----------------|
| FINE WIRE WELDER | 70825788 | 363-0351 |
| Spare Carbon Electrodes (x5) for 1.1mm 250V Fine Wire Welder | 70656473 | 814-0184 |




Thermocouple Welder Controls



IEC PTFE Insulated Twin Twisted Pair Thermocouple Cable

Available in Thermocouple Types K, J T & N



Type 'K' Type 'T'

| T/C Type | Conductors | Cores | Reel Length | Allied code | RS order code |
|----------|------------|---------------|-------------|-------------|---------------|
| J | 1/0.2mm | +Black/-White | 25 metres | 70657194 | 827-5980 |
| J | 1/0.2mm | +Black/-White | 50 metres | 70657195 | 827-5984 |
| J | 1/0.315mm | +Black/-White | 25 metres | 70657198 | 827-5993 |
| J | 1/0.315mm | +Black/-White | 50 metres | 70657199 | 827-5996 |
| K | 1/0.315mm | +Green/-White | 25 metres | 70657200 | 827-6000 |
| K | 1/0.315mm | +Green/-White | 50 metres | 70657205 | 827-6019 |
| Т | 1/0.315mm | +Brown/-White | 25 metres | 70657208 | 827-6028 |
| Т | 1/0.315mm | +Brown/-White | 50 metres | 70657206 | 827-6022 |
| J | 1/0.508mm | +Black/-White | 25 metres | 70657197 | 827-5990 |
| J | 1/0.508mm | +Black/-White | 50 metres | 70657201 | 827-6003 |
| K | 1/0.508mm | +Green/-White | 25 metres | 70657203 | 827-6012 |
| K | 1/0.508mm | +Green/-White | 50 metres | 70657204 | 827-6016 |
| J | 7/0.2mm | +Black/-White | 25 metres | 70657202 | 827-6006 |
| K | 7/0.2mm | +Green/-White | 25 metres | 70657207 | 827-6025 |
| Т | 7/0.2mm | +Brown/-White | 25 metres | 70657209 | 827-6031 |
| N | 7/0.2mm | +Pink/-White | 25 metres | 70657210 | 827-6034 |




| | Conductors | Cores | Jacket | Reel Length | Allied Code | RS order code |
|----------|--------------------|--------------------------------|--------|------------------------|----------------|----------------------|
| Extensi | on: | | | | Code | |
| KX | 7/0.2mm | +Green/-White | Green | 10 metres | 70657084 | 827-5615 |
| KX | 7/0.2mm | +Green/-White | Green | 25 metres | 70641729 | 236-3820 |
| KX | 7/0.2mm | +Green/-White | Green | 50 metres | 70657085 | 827-5619 |
| KX | 7/0.2mm | +Green/-White | Green | 100 metres | 70646156 | 611-7889 |
| KX | 7/0.2mm | +Green/-White | Green | 200 metres | 70657088 | 827-5628 |
| 101 | 770.2 | Green, white | orcen. | 200 11101103 | 70037000 | 027 3020 |
| | | | | | | |
| JX | 7/0.2mm | +Black/-White | Black | 10 metres | 70641640 | 219-4753 |
| JX | 7/0.2mm | +Black/-White | Black | 25 metres | 70657078 | 827-5592 |
| JX | 7/0.2mm | +Black/-White | Black | 50 metres | 70657079 | 827-5596 |
| JX | 7/0.2mm | +Black/-White | Black | 100 metres | 70641737 | 236-3915 |
| JX | 7/0.2mm | +Black/-White | Black | 200 metres | 70657081 | 827-5606 |
| | | | | | | |
| TV | 7/0.2 | . Danson / M/hito | D | 10 | 70644627 | 210 4702 |
| TX TX | 7/0.2mm | +Brown/-White | Brown | 10 metres | 70641637 | 219-4703 236-3870 |
| | 7/0.2mm 7/0.2mm | +Brown/-White +Brown/-White | Brown | 25 metres | 70641734 | |
| TX | | | Brown | 50 metres | 70657095 | 827-5653 |
| TX | 7/0.2mm | +Brown/-White | Brown | 100 metres | 70651749 | 762-1146 |
| TX | 7/0.2mm | +Brown/-White | Brown | 200 metres | 70657098 | 827-5662 |
| NX | 7/0.2mm | +Pink/-White | Pink | 10 metres | 70641635 | 219-4668 |
| NX | 7/0.2mm | +Pink/-White | Pink | 25 metres | 70657091 | 827-5637 |
| NX | 7/0.2mm | +Pink/-White | Pink | 50 metres | 70657089 | 827-5631 |
| NX | 7/0.2mm | +Pink/-White | Pink | 100 metres | 70657092 | 827-5640 |
| | | | | | | |
| | Conductors | Cores | Jacket | Reel Length | Allied | RS order code |
| | | | | | Code | |
| Compensa | | | | | | |
| VX (KCB) | 7/0.2mm | +Green/-White | Green | 10 metres | 70657082 | 827-5609 |
| VX (KCB) | 7/0.2mm | +Green/-White | Green | 25 metres | 70641629 | 219-4551 |
| VX (KCB) | 7/0.2mm | +Green/-White | Green | 50 metres | 70657080 | 827-5603 |
| VX (KCB) | 7/0.2mm | +Green/-White | Green | 100 metres | 70641630 | 219-4573 |
| VX (KCB) | 7/0.2mm | +Green/-White | Green | 200 metres | 70657083 | 827-5612 |
| VX (KCB) | 13/0.2mm | +Green/-White | Green | 10 metres | 70657086 | 827-5621 |
| VX (KCB) | 13/0.2mm | +Green/-White | Green | 25 metres | 70657087 | 827-5625 |
| VX (KCB) | 13/0.2mm | +Green/-White | Green | 50 metres | 70657090 | 827-5634 |
| VX (KCB) | 13/0.2mm | +Green/-White | Green | 100 metres | 70651750 | 762-1152 |
| U (RCA) | 7/0.2mm | +Orange/-White | Orange | 10 metres | 70657096 | 827-5656 |
| U (RCA) | 7/0.2mm 7/0.2mm | +Orange/-White | Orange | 10 metres 25 metres | 70646158 | 611-7902 |
| U (RCA) | 7/0.2mm 7/0.2mm | +Orange/-White | Orange | 50 metres | 70646158 | 827-5659 |
| U (RCA) | 7/0.2111111 | +Orange/-white | Orange | 30 metres | /005/05/ | 027-3039 |
| U (RCA) | 13/0.2mm | +Orange/-White | Orange | 10 metres | 70641641 | 219-4769 |
| U (RCA) | 13/0.2mm | +Orange/-White | Orange | 25 metres | 70657093 | 827-5643 |
| U (RCA) | 13/0.2mm | +Orange/-White | Orange | 50 metres | 70657094 | 827-5647 |
| RS143/08 | 316 | | | | | |
| | | | | | | |



| T/C Type | Conductors | Cores | Reel Length | Allied code | RS order code |
|----------|------------|--------------|-------------|-------------|---------------|
| KX | 1/0.2mm | +Yellow/-Red | 25 metres | 70656106 | 814-0030 |
| KX | 1/0.2mm | +Yellow/-Red | 50 metres | 70656111 | 814-0049 |
| KX | 1/0.2mm | +Yellow/-Red | 100 metres | 70656109 | 814-0042 |
| KX | 7/0.2mm | +Yellow/-Red | 25 metres | 70656110 | 814-0046 |
| KX | 7/0.2mm | +Yellow/-Red | 50 metres | 70656113 | 814-0055 |
| KX | 7/0.2mm | +Yellow/-Red | 100 metres | 70656114 | 814-0058 |
| KX | 1/0.3mm | +Yellow/-Red | 25 metres | 70656104 | 814-0024 |
| KX | 1/0.3mm | +Yellow/-Red | 50 metres | 70656107 | 814-0033 |
| KX | 1/0.3mm | +Yellow/-Red | 100 metres | 70656108 | 814-0036 |
| TX | 1/0.3mm | +Blue/-Red | 25 metres | 70656121 | 814-0080 |
| TX | 1/0.3mm | +Blue/-Red | 50 metres | 70656126 | 814-0099 |
| TX | 1/0.3mm | +Blue/-Red | 100 metres | 70656124 | 814-0092 |
| TX | 1/0.2mm | +Blue/-Red | 25 metres | 70656125 | 814-0096 |
| TX | 1/0.2mm | +Blue/-Red | 50 metres | 70656128 | 814-0106 |
| TX | 1/0.2mm | +Blue/-Red | 100 metres | 70656129 | 814-0109 |

ANSI PVC Thermocouple Extension & Compensating Cable

PVC Insulated Flat Pair (ANSI MC96.1)



| T/C Type | Conductors | Cores | Jacket | Reel Length | Allied code | RS order code |
|---------------|------------|--------------|--------|-------------|----------------|---------------|
| Extension: | | | | | | |
| KX | 7/0.2mm | +Yellow/-Red | Yellow | 25 m | 70656102 | 814-0018 |
| KX | 7/0.2mm | +Yellow/-Red | Yellow | 100 m | 70656105 | 814-0027 |
| KX | 7/0.2mm | +Yellow/-Red | Yellow | 200 m | 70656103 | 814-0020 |
| JX | 7/0.2mm | + White/-Red | Black | 25 m | 70656096 | 813-9995 |
| JX | 7/0.2mm | + White/-Red | Black | 100 m | 70656098 | 814-0005 |
| JX | 7/0.2mm | + White/-Red | Black | 200 m | 70656099 | 814-0008 |
| TX | 7/0.2mm | +Blue/-Red | Blue | 25 m | 70656119 | 814-0074 |
| TX | 7/0.2mm | +Blue/-Red | Blue | 100 m | 70656122 | 814-0083 |
| TX | 7/0.2mm | +Blue/-Red | Blue | 200 m | 70656123 | 814-0086 |
| Compensating: | | | | | | |
| VX (KCB) | 7/0.2mm | +Yellow/-Red | Yellow | 25 m | 70656127 | 814-0103 |
| VX (KCB) | 7/0.2mm | +Yellow/-Red | Yellow | 100 m | 70656130 | 814-0112 |
| VX (KCB) | 7/0.2mm | +Yellow/-Red | Yellow | 200 m | 70656131 | 814-0115 |

