


Minimum cable diameter: 3
 Maximum cable diameter:
 - with rubber bushing: 6,5
 - without rubber bushing: 8,5
 - without reduction plate: 12,5

A
B
C
D

09 67 015 0349	M3
09 67 015 0344	4-40 UNC
Part number	Screw thread

			Dot.	Name	 All Dim. in mm Orig. Size DIN A 4
			Detail.	15/11/04 TR	
			Insp.		
			Stand.		
EC00368	07/07/09	PK	HARTING EURL F-95972 Paris		
32329	15/11/04	TR			
Mod.	Dot.	Name			

D-Sub, 15 poles, top entry, straight metal hood		Maßstab/ Scale
		1,5:1
TB 09 67 015 034X		Blatt/ Page
Sub.		2 / 2

