

- 1: T5 connection (order no. AC2316)
- 2: Target puck (order no. E17327)
- 3: Bürkert solenoid valve type 6517 and 2 silencers 780780N
- 4: T5 jumper and valve plug (order no. E10844)
- 5: FC insulation displacement connector (order no. E70471)



Product characteristics

Added value package AS-i for pneumatic quarter-turn actuators

Connector	
A/B slave	
Shaft height 30 mm	
Hole spacing 80 mm	
Sensing range: 4mm [nf]	
Electrical data	
Electrical design	2 inputs / 1 output
Operating voltage [V]	26.5...31.6 DC *)
Total current consumption from AS-i [mA]	< 160
Outputs	
Digital	
Output function	transistor PNP
Measuring / setting range	
Sensing range [mm]	4
AS-i classification	
AS-i version	2.1
AS-i profile	S-7.A.E
I/O configuration [hex]	7
ID code [Hex]	A.E
Mechanical data	
Mounting	non-flush mountable
Weight [kg]	0.872
Electrical connection	


Wiring



Electrical connection

- 1: AS-i+
- 3: AS-i-

AC0019 - Added value package AS-i for pneumatic quarter-turn actuators - eclass: 27220590 / 27-22-05-90



Outputs
 3: external voltage -
 4: switching output +
 1, 2, 5: not connected

Accessories

Accessories (included)

T5 connection (order no. AC2316); Target puck (order no. E17327); Bürkert solenoid valve type 6517 and 2 silencers 780780N; T5 jumper and valve plug (order no. E10844); FC insulation displacement connector (order no. E70471)

Remarks

Remarks

*) cULus - Class 2 source required

Pack quantity

[piece]

1