


ADAPTOR M12MALE 3 POLE /M12FEMALE 4 POLE (BR.2-4)

Adapter plug M12/M12 for inputs
3-pole
4-pole

[Link to Product](#)

Illustration



Product may differ from Image

Form

41242

Technical Data

Operating voltage	max. 24 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Compression gland	Zinc die casting, matte nickel plated
Protection	IP67 inserted and tightened (EN 60529)
Material	PUR

General data

Temperature range	-25...+85 °C
Test isolation voltage	0.8 kVrms

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1