


5633/////86

Minature Paguro gel connector junction box grey, 2 cable entry 8-10mm with 3 pole terminal block



Dimensioni / Dimensions (mm)

A	B	C
38	42,5	29,5



SPECIFICATION

Cable Entries	2
Number of Poles	3
Terminal Type	Screw - wp
Body Material	Nylon PA66-RV
Colour	Grey
IP Rating	68
Max Conductor Size (Sq mm)	2.5
Max Current (A)	16
Max Voltage (V)	250
Minimum Temp Rating °C	-30
Maximum Temp Rating °C	130
Minimum Cable Diameter (mm)	8
Maximum Cable Diameter (mm)	10
Depth (mm)	(c) 29.5
Fixing System	Cable
Gel Material	Sealing bi-component syliconic gel
Length (mm)	(A) 38
Width (mm)	(B) 42.5

DISTRIBUTORS

