



**12W**

VT-828 12W LED WALL LIGHT COLORCODE:4000K,BLACK -SQUARE

Lumens <b>900</b>	Beam Angle <b>158</b>	Dimensions <b>169x100mm</b>
----------------------	--------------------------	--------------------------------

Day White  
 SKU:8544



## Technical Information

Output Voltage:	DC:36-40V	LED Chip Type:	SMD
Watts:	12	IP Rating:	IP65
Lumens:	900	Dimmable:	No
Shape:	Square	Warranty (Years):	2
Beam Angle:	158	PF:	>0.5
Output Current:	280mA	CRI:	>80
No. Of Led:	72	Operation Temperature:	-25 to +50°C
Unit Color:	Black	Input Power:	AC:220-240V,50/60Hz
Body Type:	PC	Sensor Compatibility:	Yes
Long life:	20,000 Hours		

## Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.72
Unit CBM	0.00289

### Listing Details

EAN Code	3800157638937
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	400

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES