



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/07/2017	BGATES
B	ECN 9935: REVISE DESCRIPTION AND COLOR	07/02/2019	DFRISIELLO



**PIN OUT**

P1	P2	P1	P2
1	1	16	16
2	2	17	17
3	3	18	18
4	4	19	19
5	5	20	20
6	6	21	21
7	7	22	22
8	8	23	23
9	9	24	24
10	10	C1	C1
11	11	C2	C2
12	12	C3	C3
13	13	C4	C4
14	14	C5	C5
15	15	S	S



**NOTES**

**ELECTRICAL PROPERTIES:**

1. THERE SHALL NO OPEN/SHORTS, MISWIRING OR INTERMITTENT FAILURES.
2. ADAPTER SHALL BE 100% ELECTRICAL TEST.
3. VOLTAGE TEST: DC 300V 10MS  
INSULATION RESISTANCE: 5.0M OHM/MIN  
CONDUCTOR RESISTANCE: 5.0M OHM/MAX.

**PACKAGING:**

4. ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY JYOU	DATE 07/07/2017	50 HIGH STREET NORTH ANDOVER, MA 01845		
	CHECKED BY BGATES	DATE 07/07/2017		CATEGORY AUDIO/VIDEO	
	APPROVED BY BGATES	DATE 07/07/2017	PRODUCT DESCRIPTION ADPTR DVI24+5 F TO HDMI M	REF	
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. VIC00008

SCALE: NONE    CAD FILE: VIC00008.SLDDRW    SHEET 1 OF 1