



NOTES:
 (INNER MOLD NO:GJW2011-08-063)
 (OUTER MOLD NO:H10-428)

1. MATERIAL

- 1.1 HDMI CABLE: (7/0.10BC*1P+7/0.10BC+FAM)*5PCS+7/0.10BC*4C +AL+7/0.12BC+128/0.12ALM+BLUE PVC JACKET (KE50-3015-68).
 OD: $\varnothing 6.0 \pm 0.2$ mm
 CABLE MARKING: E324703 **AW** AWM STYLE 20276 80°C 30V HIGH SPEED HDMI® CABLE WITH ETHERNET
- 1.2 HDMI 19PIN TYPE A MALE: RIVET TYPE, BLACK INSULATION, GOLD PLATED CONTACTS 3u", GOLD PLATED SHELL G/F.
- 1.3 INNER MOLD: TRANSPARENCE PE.
- 1.4 OUTER MOLD: MOLDED BLUE PVC (KE50-3015-68).

2. ELECTRICAL

- 2.1 100% OPEN AND SHORT TEST.
 - 2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.
 - 2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.
 - 2.4 HI-POT: DC300V/0.01S.
 - 2.5 HDTV-DVD TEST : 1080P.
3. PACKAGING: A PC/PE-BAG PACKAGING.
 4. ALL MATERIALS ARE RoHS COMPLIANT.

PIN OUT

P1	P2		
1	1	BLUE	RED FAM
3	3	WHITE	
5	5	DRAIN	
4	4	BLUE	SILVER FAM
6	6	WHITE	
2	2	DRAIN	
7	7	BLUE	BLUE FAM
9	9	WHITE	
11	11	DRAIN	
10	10	BLUE	BROWN FAM
12	12	WHITE	
8	8	DRAIN	
13	13	GREEN	
14	14	BLUE	GREEN FAM
19	19	WHITE	
17	17	DRAIN	
15	15	WHITE	
16	16	BLUE	
18	18	RED	
SHELL	DRAIN	SHELL	

P/N CHART

CUSTOMER NO	L(mm)
CS22239	500±30mm
CS22240	1000±30mm
CS22241	1500±50mm
CS22242	2000±50mm
CS22243	3000±70mm
CS22244	5000±70mm

LENGTH TOLERANCE: X. ± 0.5 .X ± 0.2 .XX ± 0.1		SCALE: FREE	CUS. NAME:	ENG: Jason
ANGLE TOLERANCE: X° ±3' .X° ±1'		UNIT: mm	PRODUCT NO: N/A	CHECKED: sally
VERSION: 00		1/1	CUSTOMER NO: SEE THE P/N CHART	APPROVED:
DATE 2011-10-24		DATE 1/1	PRODUCT DESCRIPTION: HDMI AM-AM/0.5m/1m/1.5m/2m/3m/5m/GOLD-PLATED	
00	NEW ISSUE			
REV.	MODIFY DESCRIPTION			