



# Platinum Resistance Pt100 4 wire class B Resistance Thermometer with Compact KNS Head





## **Quality & Service**

**About Labfacility** 

Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Formed in 1971, Labfacility specialize in the field of **Temperature and Process** 

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

### **Contact Details**

Email sales@labfacility.com

www.labfacility.com

- Pt100 probe with compact KNS terminal head
- Class B, 4 wire connection
- Various probe available lengths
- 6.0mm diameter in 316 stainless steel
- IP67 aluminium alloy weatherproof connection head
- Sensor temperature rating -50°C to +450°C
- Conforms to IEC 751

### **Specifications**

Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 wire Sensor type:

Construction: 6.0mm diameter stem in 316 stainless steel

IP67 KNS connection head Termination:

-50°C to +450°C (connection head @ 170°C) Probe temperature range:

Cable entry: M16 x 1.5mm

Probe DiaØ	Probe length	order code
6.0mm	100mm	2749484
6.0mm	150mm	2749482
6.0mm	200mm	2749485
6.0mm	250mm	2749486
6.0mm	300mm	2749487