

## Coaxial Cable Connector 11\_1023-C50-2-2/111\_N

### Description

Straight cable plug

Interface standards  
DIN 41626/2



### Technical Data

#### Electrical Data

Impedance 50 Ω  
Interface frequency max. 4 GHz

#### Mechanical Data

Centre contact crimped  
Outer contact crimped  
Weight 0.0021 kg

#### Environmental Data

Operating temperature -55 °C to 125 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

### Related Documents

Outline drawing DOU-00007352  
Catalogue drawing DOU-00006694  
Assembly instruction DOC-0000179140

### Ordering Information

Single package 11\_1023-C50-2-2/111\_NE  
Bulk 100 pcs package 11\_1023-C50-2-2/111\_NH

### Additional Information

Suitable cables K\_02252\_D, ENVIROFLEX\_316\_D, G\_02232\_D