



## Blacklight BL368 Linear T5

F11W T5 BL368  
0000097

### Optical data

Ambient temperature for maximum luminous flux (°C)	25
Light colour	BL368 Blacklight
Adjustable chromaticity	N

### Electrical data

Wattage (W)	11.00
Current (A)	0.350
Mains voltage (V)	230-240V
Product Voltage (V)	34
Control gear required	Yes
Transformer required	No
Dimmable	No
Dimming method	N/A
Drive current (mA)	350

### Lifetime data

Average life (Nominal) (h)	10000
----------------------------	-------

### Physical data

Nominal Product Length (mm)	225.0
Nominal Product Diameter (mm)	16
Max. Length base to base (mm) - A	212.1
Length base to pin Min-Max (mm) - B	216.8-219.2
Max. Lamp Length (mm) - C/L	226.3
Max. Lamp Diameter (mm) - D	17.0
Weight (kg)	0.019

### Packaging

Single packaging type	Carton
Product EAN number	5410288000978
Packaging single length / height (cm)	22.6
Packaging single width (cm)	1.9
Packaging single depth (cm)	1.9
DUN14 (outer)	15410288000975
Units per outer package	25
Packaging outer length / height (cm)	24.0
Packaging outer width (cm)	11.0
Packaging outer depth (cm)	10.5


### Safety data

Lamp mercury content (mg)	2.30
Optimal operating condition (°C)	-15-50
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes

## Blacklight BL368 Linear T5 F11W T5 BL368 0000097

<b>Intended purpose</b>	Flykilling - Insect attraction
<b>Suitable for household illumination</b>	No
<b>Safety message</b>	Not suitable for household

### PHOTOMETRY



### TECHNICAL DRAWINGS

