

Coloured T8 F18W/T8/BLUE 0002563



Product features

- Coloured T8



PRODUCT OVERVIEW

Product name	F18W/T8/BLUE
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T8
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	SPG
ETIM Class	EC000108
E-number FI	4942918
E-number SE	8356732
E-number Norway	3830220
Luminous flux (lm)	300
Light colour	Blue
Wattage (W)	18.00
Product Voltage (V)	57
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	8000
Product EAN number	5410288025636

DATA TABLE

General data

Product name	F18W/T8/BLUE
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T8
Cap/Base	G13

Coloured T8 F18W/T8/BLUE 0002563

Lamp finish	Frosted/Coated
Fixture rating	Open
General application	SPG
ETIM Class	EC000108
E-number FI	4942918
E-number SE	8356732
E-number Norway	3830220

Optical data

Luminous flux (lm)	300
Ambient temperature for maximum luminous flux (°C)	25
Light colour	Blue
Adjustable chromaticity	N

Electrical data

Wattage (W)	18.00
Watt (Rated) - High frequency (W)	16.00
Current (A)	0.370
Product Voltage (V)	57
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	370

Lifetime data

Average life (Nominal) (h)	8000
Average life (Rated) (h)	8000

Physical data

Nominal Product Length (mm)	600.0
Nominal Product Diameter (mm)	26
Max. Length base to base (mm) - A	589.8
Length base to pin Min-Max (mm) - B	594.5-596.9
Max. Lamp Length (mm) - C/L	604.0
Max. Lamp Diameter (mm) - D	28.0
Weight (kg)	0.083

Packaging

Single packaging type	Carton
Product EAN number	5410288025636
Packaging single length / height (cm)	61.0
Packaging single width (cm)	2.9
Packaging single depth (cm)	2.8
DUN14 (outer)	15410288025633
Units per outer package	25
Packaging outer length / height (cm)	63.0
Packaging outer width (cm)	15.5

Coloured T8 F18W/T8/BLUE 0002563

Packaging outer depth (cm) 15.0

Safety data

Lamp mercury content (mg)	2.80
Breakage cleaning instructions	Applicable
Special purpose lamp	Yes
Suitable for household illumination	Yes

TECHNICAL DRAWINGS

