

Clamps with locknut



Version:

- Spindle made from heat-treated steel
- Basic body painted
- Spindle head burnished
- With locknut
- Clamps without support

Advantage:

- Swivel mounted ball minimises contact friction
- No transfer of rotational forces to the workpiece through spindle movement.

Art. no.	26160 030
Min./max. support plate height	200-320 mm
Load-carrying capacity	4000 kg
Width across flats	46 mm
Length	160 mm
Width	22 mm
Width 1	90 mm
Spindle diameter	30 mm



EAN-Code

4020772072575