

## Pneumatic hose drum ST 200 rotatable

Length 30 m

**metabo**<sup>®</sup>

### Application:

For space-saving storage of pneumatic hoses and rolling up correctly.

<b>Art. no.</b>	<b>75014 210</b>
<b>Model</b>	ST 200 pivot-mounted
<b>Type</b>	Rotatable
<b>Hose length</b>	30 m
<b>Inner hose diameter</b>	9 mm
<b>Outer diameter of hose</b>	12.5 mm
<b>Weight</b>	8 kg
<b>Material of drum body</b>	Plastic
<b>Max. operating pressure</b>	12 bar
<b>Material of hose</b>	Polyurethane
<b>With connection male coupling</b>	Yes

### EAN-Code

4003665361086

