

KERN MWS400K100DM

Rollstuhlwaage mit niedriger Bauhöhe für bequemes Auffahren - mit Eich- und Medizinzulassung



Measuring system

| | |
|-------------------------------|----------------------|
| Adjustment options: | External calibration |
| Linearity: | 100 g 200 g |
| Readout [d]: | 100 g 200 g |
| Recommended adjusting weight: | 400 kg (M1) |
| Reproducibility: | 100 g 200 g |
| Resolution: | 3 2.000 |
| Warm up time: | 10 min 10 min |
| Weighing range [Max]: | 300 kg 400 kg |
| Weighing system: | Strain gauge |
| Weighing units: | kg |

Display

| | |
|-----------------------|----------|
| Display digit height: | 2,500 cm |
|-----------------------|----------|

Technical data about verification

| | |
|---|---------------|
| Minimum load [Min]: | 2 kg |
| Periodic Verification for Italy: | 969-112 |
| Verification approval conforming to 2014/31/EU: | yes |
| Verification by KERN possible: | yes |
| Verification class: | III |
| Verification value [e]: | 100 g 200 g |

Functions

| | |
|--|-----|
| BMI function: | yes |
| Data hold function: | yes |
| PRE-TARE function: | yes |
| Vibration-free weighing (Animal weighing program): | yes |

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 35 °C |
| Minimum ambient temperature: | 5 °C |

Power supply

| | |
|----------------|--------------------------|
| Charging time: | 14 h |
| Input voltage: | 100 V - 240 V 50 / 60 Hz |
| n/a: | CH EURO UK |

| | |
|------|------------------------|
| n/a: | Mains adapter external |
|------|------------------------|

Power supply

| | |
|---------------------------------|----------------------------------|
| Operating time: | 50 h |
| Operating time (Backlight off): | 45 h |
| Rechargeable battery: | Rchrg. battery optional - intern |

Service

Adjustment at the location of installation: 961-250

| | |
|--------------------|---------|
| DAkkS Certificate: | 963-130 |
| Verification: | 965-130 |

Category

| | |
|----------------|---------------------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Wheelchair platform scale |

Packaging & shipping

| | |
|-------------------------------|----------------------|
| Delivery: | 48 h |
| Dimensions packaging (WxDxH): | 1420 x 1200 x 130 mm |
| Gross weight: | 52,600 kg |
| Net weight: | 42,200 kg |
| Shipping method: | Freight forwarder |

Construction

| | |
|---------------------------------------|---------------------|
| Cable length: | 1,800 m |
| Cable length of display device: | 1,800 m |
| Casing material: | Steel lacquered |
| Dimensions of display device (WxDxH): | 210 x 110 x 50 mm |
| Dimensions of weighing plate (WxDxH): | 1255 x 1060 x 60 mm |
| Level indicator: | yes |
| Material weighing plate: | Steel lacquered |
| Overall dimensions mounted (WxDxH): | 1255 x 1060 x 69 mm |
| Revolving screw feet: | yes |
| Wall mount: | yes |
| Weighing surface (WxD): | 1000 x 1000 mm |