

## PeakTech® TF-30 PROD-ID: P TF-30

### Surface Temperature Probe, -50 ... +500 °C

This temperature probe is typ-K-thermocouples (NiCrNi). This probe is suitable for all of our thermometers published in our catalogue.



Model	P TF-30
Ranges	-50 °C.....+500 °C/ -58 °F...+932 °F
Accuracy	± 2 %
Cable length	200 cm
Probe length	200 mm
Probe	14,0 mm
EAN-13	4250569401657

