


Lumina

Lumina Curve LED 2700K

3039983



Product features

- Ambient decorative Curve LED rectangular horizontal wall light with direct / indirect lighting to provide a soft lighting effect, 2700K amber white colour temperature, white aluminium body and integrated LED (non-dimmable) driver, 355 lumens, 6W, 59lm/W, 2700K, IP20, RAL 9003



PRODUCT OVERVIEW

Product name	Lumina Curve LED 2700K
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted
Environment	Internal
General application	Hospitality, Residential & Consumer
ETIM Class	EC002892
E-number FI	4271114
E-number SE	7502646
Warranty	3 years
Fixture luminous flux (lm)	355
Luminaire efficacy (lm/W)	59
LOR (%)	100
Colour temperature (K)	2700
Light colour	Amber White
CRI (Ra)	85
Total power consumption (W)	6
Electrical protection	Class II
Control gear type	LED driver constant current
Dimming method	N/A
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	8711971399834

DATA TABLE

General data

Product name	Lumina Curve LED 2700K
Technology	LED
Housing	Aluminium
Mount	Wall surface mounted

Lumina

Lumina Curve LED 2700K

3039983

Environment	Internal
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4271114
E-number SE	7502646
Warranty	3 years

Optical data

Fixture luminous flux (lm)	355
Luminaire efficacy (lm/W)	59
LOR (%)	100
Colour temperature (K)	2700
Light colour	Amber White
CRI (Ra)	85
Adjustable chromaticity	N

Electrical data

Total power consumption (W)	6
Mains voltage (V)	100-240V
Electrical protection	Class II
Control gear type	LED driver constant current
Transformer required	No
Dimming method	N/A
Drive current (mA)	500
Energy Efficiency Class (A->G) of contained light source	F

Lifetime data

Lifespan L70 B50	50000
Lifespan L80 B20	35000
Lifespan L90 B10	25000

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	106
Nominal Product Width (mm)	188
Nominal Product Height (mm)	67
Weight (kg)	0.538

Packaging

Single packaging type	Carton
Product EAN number	8711971399834
Packaging single length / height (cm)	19.43
Packaging single width (cm)	12.73
Packaging single depth (cm)	7.63

Lumina Lumina Curve LED 2700K 3039983


DUN14 (outer)	18711971399831
Units per outer package	20
Packaging outer length / height (cm)	41.5
Packaging outer width (cm)	27.3
Packaging outer depth (cm)	40.6

PHOTOMETRY

Distance [m]	Cone diameter [m]	E ₀ [lx]	E _{10%} [lx]	E _{5%} [lx]
0.5	2.86	290	70.7	5
1.0	5.71	68	17.2	1
1.5	8.57	29	7.1	0.5
2.0	11.42	16	4.0	0.3
2.5	14.28	10	2.5	0.2
3.0	17.13	7	1.8	0.1

Distance [m] Cone diameter [m] Illuminance [lx]

— C0 - C180 (Half beam angle: 141.4°)



TECHNICAL DRAWINGS

