

SC torus milling cutter

4 cutters, ULTRA-coated

Application:

Torus milling cutter for universal machining.

Execution:

- Solid carbide ultra-fine grain
- Straight shank in accordance with DIN 6535 HB
- ULTRA-coated
- Centre cutting
- Twist angle 35°/38° with unequal cutting pitch
- Edge radius
- 2-fold twisted internal coolant supply to front cutters
- With clearance



Art. no.	16839 378
Cutting material	SC
Surface	ULTRA
Type	N
Number of cutting edges	4 PCS
Twist angle	35°, 38°
Tool holding device	HB parallel shank
Construction length	Normal
Cutting edge diameter	20 mm
Cutting edge length	38 mm
Clearance length	54 mm
Length	104 mm
Clearance diameter	19.5 mm
Shank diameter	20 mm
Edge radius	1.5 mm
fz steel 1000	0.12 mm
Gross Weight	0.400 kg
Product Group	148