

## 3-point internal micrometer

**ORION®**

### Application:

For measuring through-bores and short centring shoulders.

### Execution:

- Scale with anti-glare, brushed chromium plated finish
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force

### Delivery:

Single device with setting ring and measuring depth extension in a case



|   |                                |
|---|--------------------------------|
| <b>Art. no.</b>                         | <b>31910 016</b>               |
| <b>Brand</b>                            | ORION                          |
| <b>Manufacturer Part Number</b>         | 31910016                       |
| <b>Min./max. length measuring range</b> | 16-20 mm                       |
| <b>Measuring depth</b>                  | 80 mm                          |
| <b>Error limit</b>                      | 4 µm                           |
| <b>Vernier scale</b>                    | 0.005 mm                       |
| <b>Extensions provided</b>              | 150 mm                         |
| <b>Measuring spindle increments</b>     | 0.5 mm                         |
| <b>Adjusting ring diameter</b>          | 16 mm                          |
| <b>Calibration Group</b>                | I, AC                          |
| <b>DIN</b>                              | 863                            |
| <b>Calibration Group Description</b>    | Internal micrometers (3 point) |
| <b>Gross Weight</b>                     | 1.000 kg                       |
| <b>Product Group</b>                    | 3BB                            |

### EAN

4039247459490