

Flat magnetic grips, hard ferrite core, steel jacket

With threaded bush

ORION[®]

Application:

Auxiliary materials with universal application during clamping, assembling, lifting and welding operations, and for installing in devices etc.

Version:

- With hard ferrite core
- Surface galvanised
- Magnetic shielding
- With threaded bush
- Operating temperature up to 100°C

| | |
|---------------------------|------------------|
| Art. no. | 51145 590 |
| Outer diameter | 80 mm |
| Height | 34 mm |
| Height of the base | 18 mm |
| Thread dimension | M10 |
| Adherence strength | 550 N |
| Thread length | 16 mm |



EAN-Code

4039247261888