

Pneumatic impact screwdriver E 27 P

MANNESMANN
DEMAG

Delivery

Threaded sleeve, impact grease, oil bottle

Art. no.	75061 355
Model	E 27 P
Suitable for screw	M14 - M24
Max. tightening torque	1600 Nm
Max. idle speed	5400 rpm
Air consumption	15 l/s
Tool holding device	3/4-inch external square
Hammer mechanism system	3 jaws striking mechanism
Length	182 mm
Connection thread	IT 1/2 inch
Inner hose diameter	13 mm
Sound-pressure level	94 dB
Weight	5.95 kg
With right/left-hand rotation	Yes



EAN-Code

4251757301926