

PCB Terminal Blocks

2.54mm pitch



SPECIFICATION:

Material

Shrapnel	Stainless steel (SUS301)
Pin Header	Brass, Tin Plated
Housing	PA66, UL94V-0

Electrical

Standard	IEC	
Rated Voltage	150V	130V
Rated Current	2A	6A
Wire Range	26-20AWG	0.14-0.5mm ²
Contact Resistance	20mΩ	
Insulation Resistance	500MΩ/DC500V	
Withstand Voltage	AC1300V/1Min	

Mechanical

Temperature Range	-40°C~+105°C
Max. Soldering	+250°C for 5 sec
Strip Length	11mm

Size

Pitch	2.54mm (.100")
Poles	1P

