






DIL SOCKETS „THROUGH HOLE“
ID: 023 MP-RELAIS

Series 121



TECHNICAL DATA

Pitch	2,54 mm
Insulating Material	high temp. thermoplast UL94V-0
Contact Material	Brass/BeCu
Rated Current	1 Amp.
Rated Voltage	100 V _{RMS} /150 V _{DC}
Breakdown Voltage	min. 1000 V _{RMS}
Operating Temperature	-55°C bis +125°C
Maximum Soldering Temperature	260°C for 10 seconds



Code	Drawing	Poles	Loaded pins
14.3	A	4	... pin 1/7/8/14
14.3	B	8	... pin 1/2/6/7/8/9/13/14
16.3	C	8	... pin 1/4/6/8/9/11/13/16

Other layouts upon request.

All dimensions in mm.
 Other dimensions upon request.

MP XX.Y XXX XXX U

Code: see table _____
 XXX: STG B = sleeve: Sn / clip: Au _____
 Poles: 4 - 8 poles possible _____
 U: RoHS-compliant with high temp. plastic _____