

Crimp Terminal Housings, 3.96mm






Specification

Current Rating	7A AC,DC
Voltage Rating	250V AC/max
Operating Temperature	-25°C...85°C
Insulation Resistance	1000MΩ/min
Contact Resistance	10mΩ/max
Terminal Material	Brass, tin-plated
Material	Nylon 66, UL94V-0
Colour	White

Product Range:

	Poles
RND 205-00975	2
RND 205-00976	3
RND 205-00977	4
RND 205-00978	5
RND 205-00979	6
RND 205-00980	8



Poles	Dimensions mm (in.)	
	A	B
2	3.96 (0.156)	8.04 (0.317)
3	7.92 (0.312)	12.10 (0.476)
4	11.88 (0.468)	15.96 (0.628)
5	15.84 (0.624)	20.0 (0.787)
6	19.8 (0.780)	23.9 (0.941)
8	27.72 (1.074)	31.86 (1.254)