### Double icon illuminated pushbuttons - bushing Ø 24 or 26 mm - momentary or latching

Distinctive features and specifications



- Double icon actuator
- Snap-in and threaded bushing models
- Suited for integrated designs
- Large but lightweight
- □ Sealed to IP69K (threaded bushing version)

#### **ELECTRICAL SPECIFICATIONS**

- Max. current/voltage rating with resistive load : - silver contacts (code 2) : 4A 12VDC
- gold plated contacts (code 4) : 200mA 12VDC • Initial contact resistance : 50 m $\Omega$  max.
- Insulation resistance : 1 G $\Omega$  min. at 500VDC
- Dielectric strength : 1.000 Vrms 50 Hz min.
  Electrical life at full load :
- - Momentary models : 1 million cycles (gold plated contacts) 400.000 cycles (silver contacts)
- Latching models : 200.000 cycles

#### **GENERAL SPECIFICATIONS**


• Front panel sealing :

- Threaded bushing version : IP69K according to DIN 40050-9 Snap-in version : IP54 according to IEC 60529 with panel gasket and
- 2 mm panel thickness
- Panel thickness :
  - Snap-in version : 1,5 (.059) to 2 mm (.078) with panel gasket 2 (.078) to 2,5 mm (.885) without panel gasket
  - Threaded bushing version :1(.039) to 18 mm (.708) max.
- Total travel : 2,5 mm ± 0,5 mm
- Typical operating force : 8N ± 2N
  Low level or mechanical life :
- Momentary models : 1 million cycles
- Latching models : 200.000 cycles
- Torque : 3 Nm max. applied to nut
- Operating temperature : -40°C to +75°C



FD1506-A


- Case : PA46
- Actuator : PA12
- Bushing/ bezel : PA66
- Contacts : silver (code 2)
- or silver, gold plated (code 4)



The company reserves the right to change specifications without notice.

### Double icon illuminated pushbuttons - bushing Ø 24 or 26 mm - momentary or latching

Overview



#### **ABOUT THIS SERIES**

On the following pages, you will find successively : model structure of switches and options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



NOTICE : please note that not all combinations of above numbers are available. Refer to the following pages for further information.


Mounting accessories : Standard hardware supplied : 1 hex nut (threaded bushing version) and 1 panel gasket



ø

Packaging unit : 20 pieces


### Double icon illuminated pushbuttons - bushing $\emptyset$ 24 or 26 mm - momentary or latching



- Solder lugs
- Flat actuator


To order a product, replace • with one of the codes selected under "LED control and number of poles" below, then add the desired options.





#### LED CONTROL AND NUMBER OF POLES

Complete the model numbers above with one of the following codes.



dotted line = jumper to be wired by the user. LED- has to be wired to one pin of pole 2.

## Double icon illuminated pushbuttons - bushing Ø 24 or 26 mm - momentary or latching

Options

CONTACT MATERIALS
<ul> <li>2 Silver</li> <li>4 Silver, gold plated</li> </ul>
8 Smoke black
BEZEL COLOR
2 Black
LED COLOR
F Red/green
LED RESISTOR
<ul> <li>No resistor supplied</li> <li>1 12V resistor</li> <li>2 24V resistor</li> </ul>
SYMBOLS
3 START (green) / STOP (red) with ring
4 ON (green) / OFF (red) with ring $OFF$ (red) V(green) / O(red)
5 I (green) / O ( red) with ring