

## T-coupler M12 female /M12 female - M12 male

T-coupler M12 – M12  
5-pole  
Parallel circuit

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Form

42751

#### Technical Data

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

#### General data

Temperature range	-25...+85 °C
-------------------	--------------

#### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1