

MEN POWER SUPPLY 1/2-PHASE, SMOOTHED

IN: 115/230+/-10VAC OUT: :24V/10ADC


Current: 10 A

Output rating: 240 W


This power supply units meet the (EN 61000-3-2) standard for harmonic current. For any mounting position at vertical wall.

[Link to Product](#)

Illustration



stay connected



Product may differ from Image

Approvals



Input

Input voltage	115/230 V AC \pm 10 V AC
Input current	3.7 A (115 V AC); 1.85 A (230 V AC)
Input fuse (external)	5 A (T) (115 V AC); 2.5 A (T) (230 V AC)
Frequency	50...60 Hz

General data

Standards	(EN 61558-2-6), (EN 62041 category I), (EN 55011 B), (EN 61000-3-2)
Mounting method	Key-hole mounting
Dimensions H x W x D	112.5x120x160 mm
Fixing centers a x b x c	94.5x90x5.8 mm
Temperature range	-20...+60 °C, no condensation

Output

Output voltage	24 V DC (SELV)
Output current (Ta 60/40 °C)	max. 10 A (115 V AC); 12 A (230 V AC)
Ripple	max. 5 %rms
Output fuse	20 A (automotive fuse FKS)
Output filter	LED, VDR and smoothing capacitor

Commercial data

country of origin	CZ
customs tariff number	85044090
minimum order quantity	1