

SIMATIC WINCC RT UPGRADE ASIA FROM V7.0 TO V7.2, FOR SIMATIC WINCC RUNTIME (RT) INCL. OPTIONS REDUNDANCY, SERVER, USER ARCHIVE, WEB NAVIGATOR, WEB NAV LOAD-BALANCING, WEB DIAG CLIENT/SERVER, DATA MONITOR, CONNECTIVITY PACK, CONNECTIVITY STATION RUNTIME & CONFIGURATION -SW ON DVD, SINGLE LICENSE, LICENSE KEY ON USB-STICK

General information

Multi-user system	
• Multiuser capability	Yes
• Number of servers, max.	18
• Number of clients for server without operator console, max.	32
• Web clients	Yes

Operator control and monitoring

Object block library	Yes; Integrated
Alarm logging system (incl. buffer and acknowledgment)	Yes; Integrated
Report system/log system	Yes
SQL database	Yes; Integrated
Process diagnostics	No
Sector-specific and technological expansions	Yes
Recipes/user archives	
• User archive/recipe management	Yes

Interfaces

Programming interfaces	Yes
OPC-DA interface, Server	Yes
OPC-DA interface, Client	Yes

Hardware requirements

Processor clock frequency, min.	1 GHz
Main memory, min.	1 Gbyte

Operating systems

Executable for operating system	
• Windows 7	Yes

Configuration

Number of multi-user configurations, max.	32
Online configuration	Yes

Script languages (Runtime)

- Number of Visual Basic Scripts Yes
- other Yes

Know-how protection

- Password protection Yes

Languages

Configuration languages

- Number of configuration languages 70

last modified: 12.03.2015