

MECHANICAL DETAILS

Shell Style Model EG* : Fixed receptacle nut fixing


Keying

Housing Material Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces

Cable Fixing 0 - 0 mm

Variant 2 :

	A	B	e	E	L	M	N
Mm.	15.5	10.6	M12x1.0	6	23	1.8	21.5
In.	0.61	0.42		0.24	0.91	0.07	0.85



PERFORMANCE DETAIL

Insert :

Insulator

Specifications

Contact Type: Solder



OTHER CHARACTERISTICS

Shell Style/Model Libellé

Temp (min) -55°C

Temp (max) +200°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]

Salt Spray >144 hr

Climatical 50/175/21

Shielding (min): 75 dB (10 MHz)







Shielding (min): 40 dB (1 GHz)

IP Rating 68

Available Download

 [T_series_en.pdf](#)

Related links

-  [Contact](#)
-  [Quote Request](#)
-  [Catalogs Downloads](#)
-  [Catalogs Requests](#)
-  [Sample Request](#)
-  [3D drawings](#)