





RoHS compliant



suitable for cable AWG 20 (single solid wire)

MATERIALS

- Insulator: Thermoplastic UL 94-V-0 white
- Contact: Machined / Copper alloy
- Contact finish: Quality class 2
- Shell: steel tin plated

CHARAKTERISTICS

- Working voltage: 60V
- Current rating: 5A
- Contact resistance: max. 10mΩ - DIN41652
- Insulation resistance: >5GΩ
- Temperature range: -55° to +125°C

| General tolerances (Deltron standard) | | | |
|---------------------------------------|------------------|----------------|-----------------|
| size in mm | tolerances | | |
| | > 0.5 up to 3 | > 3 up to 6 | > 6 up to 30 |
| ±0.1 | ±0.2 | ±0.2 | ±0.3 |

| | | | | | | | |
|------------|----------------------|------|------|--|----------------------|------------------------|----|
| | All dimensions in mm | Rev. | Rev. | Rev. | DE008386 part no. | | |
| | | Rev. | Rev. | Rev. | | | |
| HD-D15SZ/2 | | | | 1.5:1 scale | drawn | 22.06.2012 | mw |
| | | | | | checked | | |
| | | | | | approved | | |
| | | | | Industrie Neuhof 8c CH-3422 Kirchberg www.d-sub.swiss | | K060072 drawing no. | |