

Uni-Dicht-Verschraubung Pg 11, 7-10,5mm



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|-------------------|-------------|
| Category | Accessories |
| Type of accessory | Cable gland |

Technical characteristics

| | |
|--|--|
| Tightening torque | ≤10 Nm (depending on the cable and the seal insert used) |
| Wrench size | 20 |
| Limiting temperature | -40 ... +130 °C |
| Degree of protection acc. to IEC 60529 | IP68 |
| Size | Pg 11 |
| Clamping range | 7 ... 10.5 mm |

Material properties

| | |
|--------------------------------------|---|
| Material (cable glands) | Metal |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326) |
| California Proposition 65 substances | Yes |

Material properties

| | |
|--------------------------------------|----------------|
| California Proposition 65 substances | Lead Nickel |
|--------------------------------------|----------------|

Commercial data

| | |
|--------------------------------|---|
| Packaging size | 10 |
| Net weight | 27 g |
| Country of origin | Germany |
| European customs tariff number | 74122000 |
| GTIN | 5713140001633 |
| eCl@ss | 27140801 Screwed cable gland (electrical) |
| ETIM | EC000441 |
| UNSPSC 24.0 | 39121431 |