

Clamping screw sets



Execution:

- Tempered
- Strength class 8 or 10
- Different clamping heights can be set as required using extension nuts and studs (extension studs).
- Widths across flats are in accordance with ISO standard (DIN ISO 272)

Delivery:

In a sturdy, high-quality wooden box with removable hinged lid.



Art. no.	26209 100
Brand	AMF
Manufacturer Part Number	82982
Suitable for groove width	10 mm
Thread dimension	M10
Number of DIN 787 T-slot screws	2 x M10 x 40 mm, 4 x M10 x 63 mm, 4 x M10 x 100 mm
Number of DIN 6379 stud bolts (extension pin)	4 x M10 x 50 mm, 4 x M10 x 80 mm, 4 x M10 x 200 mm
Number of DIN 6330 B high nuts	4 PCS
Number of extension nuts	4 PCS
Wooden box length	254 mm
Wooden box width	188 mm
Wooden box height	32 mm
Gross Weight	2.000 kg
Product Group	260

EAN

4020772082987