



Datenblatt - Fiche technique - Data sheet

11.04.5803





ROLINE PREMIUM HDMI Ultra HD Kabel mit Ethernet, ST/ST, 3,0 m

ROLINE PREMIUM Câble HDMI Ultra HD avec Ethernet, M/M, 3,0 m


ROLINE PREMIUM HDMI Ultra HD Cable + Ethernet, M/M, 3.0 m

HDMI19M



L

HDMI19M



Electroinc Test:


- Insulation Resistance: 10mΩ
- Conduction Impedance: 5Ω
- High-Pressure Test: 300V

11. 04. 5801	Premium HDMI Ultra HD Cable + Ethernet, M/M, 1m(3ft)
11. 04. 5802	Premium HDMI Ultra HD Cable + Ethernet, M/M, 2m(6ft)
11. 04. 5803	Premium HDMI Ultra HD Cable + Ethernet, M/M, 3m(10ft)
11. 04. 5804	Premium HDMI Ultra HD Cable + Ethernet, M/M, 4.5m(15ft)

Description:

- 1 Cable UL20276 (26AWG*1P+AL+D+M)*5C+26AWG*4C+M+AL+D+B, OD=8.5mm, Color: Black
- 2 Braid 1/2 Black+1/2 Transparent PET Braid
- 3 Connector HDMI 19P, Gold Plated, RoHS
- 4 Solder Lead Free Solder Wire OD=0.8mm, 1000G
- 5 Tube φ1.0 RoHS
- 6 Tube φ3.0mm RoHS
- 7 Inner mold LD-PE 950 PE RoHS
- 8 Mask 1.8cm RoHS
- 9 Copper foil 2.2cm RoHS
- 10 Outer mold Black PVC A813 45P RoHS
- 11 Metal shell Metal Shell Gold Plated 29*20.5*12.5mm, Laser Mark "PREMIUM", "HDMI"
- 12 Cover HDMI M PE Cover

Pin Out:



REV.	DATE	CONTENTS OF CHANGE	DESIGNER	TOL ±								APPROVAL	CHECK	DRAWING	DESIGN	DRAWING NAME	ROLINE Premium HDMI Ultra HD Cable + Ethernet, AM / AM, black		
				RANGE	Plc	Met	Ins	Por	Cab	Pac	Gas						DIS	DATE	PART NO.
△				0~6	0.1	0.1	0.1	0.2	0.5	1	0.5	0.2	Allen	Allen	Philip	2016-05-6			
△				6~30	0.1	0.1	.15	.25	1	1	0.5	.25							
△				30~80	0.1	.15	0.2	0.3	2	1.5	1	0.3							
△				80~180	.15	.15	.25	0.3	2	2	1	.45							
△				180~315	.15	0.2	0.3	0.4	2.5	2	1	0.6							
△				315~800	0.2	0.3	0.4	0.5	3	3	2	1.1	SCALE	1:1	UNIT	MM			