

Conical drill bit HSS, uncoated

For universal use up to 1000 N/mm²

ORION[®]

Application:

For producing bores in thin sheets made from steel, non-ferrous metals and cast iron. Also suitable for all plastics, for hard paper and plywood, as well as all materials of similar structure and strength

Execution:

- Profile-ground to meet the highest requirements for dimensional accuracy and process reliability

Advantage:

- Innovative cutting geometry: All bores are burr and chatter free
- User-friendly regrinding: Drills can be reground repeatedly
- No deformations even with the thinnest material thicknesses



Art. no.	11400 030
Brand	ORION
Manufacturer Part Number	1 1400030
Cutting material	HSS
Surface	Uncoated
Tool holding device	Cylinder shank
Type	3
Min./max. cutting edge diameter	26-40 mm
Shank diameter	12 mm
Length	92 mm
DIN	344
Gross Weight	0.400 kg
Product Group	103

EAN

4039247035175