

PDJN clamp holder, negative, right

For copy turning and longitudinal turning using DN indexable insert

ATORN[®]

Application


For copy turning and longitudinal turning using DN indexable insert 55°.

Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type D, 93° pitch angle, 55° tip angle, 0° clearance angle

Advantage

- very slim geometry, optimised for contour turning with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths
- wide range of delivery: suitable for both finishing and roughing



Art. No.	17838 006
ISO name	PDJN R/L 2020 K11
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	28 mm
Programming size	25 mm
Suitable for indexable inserts	DN.. 1104..
Tool design	Right
DIN	4983

EAN-Code

4050293126792