




Pencil Grinders and Mini Grinders / Sanders
Crayons Graveur et Mini Meuleuses / Ponçouses
Gravierstifte und Klein-Schleifmaschinen / -Poliermaschinen
Lápices de grabación y Mini Amoladoras / Lijadoras
Smerigliatrici per Stampi e Mini-smerigliatrici / Levigatrici

Pencil Grinders
 Crayons graveurs
 Turbokleinschleifmaschine
 Amoladoras a lápiz
 Smerigliatrici per stampi



DG600G2-EU

Options



Ø 3 mm ref. **47568-2** – Ø 3/32" ref. **47568-3**



See burrs page 17 – Voir fraises page 17 –
 Fräser siehe Seite 17 – Véanse fresas página 17 –
 Per le frese, vedere pagina 17.



EP50-EU

Options

- Fine point, medium point and coarse point styli
- Stylet à pointe fine, pointe moyenne et pointe grossière
- Feinstrich / Mittelstrich / Grobstrich-Graviernadel
- Punta Fina – Punta Mediana – Punta Gruesa
- Punta Fine – Punta Media – Punta Grossa

- Ref. **EP50-515**
- Ref. **EP50-516**
- Ref. **EP50-517**

- Stylus Grinding Collet – Ref. **EP50-514**
- Pince d'affûtage de stylet – Ref. **EP50-514**
- Graverspannzange – Ref. **EP50-514**
- Pinza para puntas – Ref. **EP50-514**
- Pinza per punte – Ref. **EP50-514**

Standard Equipment

DG600G2-EU & GH011A-600-EU

- Collet with 1/8" insert • Collet wrenches nos 47579, 47580 • 1.8 m x 6 mm ID air hose and 0.45 m long exhaust overhose.
- Pince, diamètre 1/8" • Clés pour pince réf. 47579, 47580 • Flexible d'alimentation 1,80 m (Ø int. 6) et gaine d'échappement longueur 0,45 m.
- Spannzange mit 1/8" - Einsatz • Spannzangenschlüssel: Nr. 47579, 47580 • Luftschilauch 1,8 m x 6 mm ID und Abluftschlauch (0,45 m).
- Pinza, diámetro 1/8" • Llaves para pinza ref. 47579, 47580 • Manguera de alimentación 1,80 m (Ø int. 6) y escape longitud 0.45 m.
- Pinza diametro 1/8" • Chiavi per pinza rif. 47579, 47580 • Flessibile d'alimentazione 1,80 m (Ø int. 6) e guaina di scarico lunghezza 0,45 m.

DG600G2K-EU

- Same as above delivered together with six 1/8" shank carbide burrs in a molded carrying case.
- Identique à la description ci-dessus et fourni en coffret avec six fraises carbure Ø de tige 1/8".
- Ausführung wie oben. Zusätzlich im Lieferumfang : Sechs Hartmetallfräser und Tragekoffer.
- Idéntico a la descripción más arriba y suministrado en estuche con seis fresas carburo Ø de varilla 1/8".
- Identico alla descrizione riportata sopra e fornito in valigetta con sei frese al carburo Ø stelo 1/8".









Standard Equipment



EP50-EU

- Molded carrying case with EP50 engraving pen • Air hose • 3 assorted styli: fine point stylus (black), medium point stylus (steel color) and coarse point stylus (green). – Knurled zoom throttle – Variable speed.
- Coffret plastique avec crayon graveur EP50 • Flexible d'alimentation • Trois stylets assortis: fin (noir), moyen (couleur acier) et grossier (vert). Commande zoom moletée – Vitesses variables.
- Tragekoffer, kpl. mit Gravierstift EP-50 • Flexibler Luftschilauch • Drei unterschiedliche Graviernadeln: Feinstrich (schwarz), Mittelstrich (stahlfarbig), Grobstrich (grün). - Gerändelter Varioregler - Variable Drehzahlregulierung.
- Caja de plástico con lápiz de grabación EP50 • Manguera de alimentación • Tres estiletes surtidos: fino (negro), mediano (color acero) y grueso (verde). Mando zoom moleteado – Velocidades variables.
- Valigetta di plastica con penna per incisione EP50 • Flessibile d'alimentazione • Tre stilo assortiti: fine (nero), medio (color acciaio) e grossolano (verde). Comando zoom a rotella - Velocità variabile.

Specifications at 90 psi – Caractéristiques à 6,2 bar – Technische Daten bezogen auf 6,2 bar – Especificaciones a 6,2 bar – Caratteristiche a 6,2 bar

Ref.	 1 min.	 1 min.						
		rpm	in	kg	mm	mm	in (NPT)	mm
DG600G2-EU	–	60 000	1/8	0.40	136	9	1/8	6
DG600G2K-EU	–	60 000	1/8	0.40	136	9	1/8	6
GH011A-600-EU	–	60 000	1/8	0.40	136	9	1/8	6
EP50-EU	18 750	–	–	0.14	137	8	1/8	6