

ROLINE 19-inch server rack 42 U, 600x1000 WxD black

Product No.	26.21.0160
Manufacturer	ROLINE
Manufacturer No.	26.21.0160
EAN (single piece)	7630049601635



ROLINE 19 inch server rack 42 U 600x1000 WxD black

The server enclosures in the ROLINE Pro series have been specially developed for convenient and flexible network cabling. Inlets with brushes, a slide-on inlet with a foam rubber seal and an additional brush inlet in the base chassis are located on the sides of the roof and base (from 800 mm enclosure width), offering a wide range of possible applications. Perforated single-leaf front doors and double-leaf rear doors, each with a swivel handle and profile half cylinder, ensure improved air circulation. The roof has a perforated cover that allows easy installation of a fan module.

Two pairs of galvanised 19" profile rails are mounted inside the cabinet, which are equipped with height units that can be read in both directions and are adjustable in depth. They are also connected with depth braces. Each cabinet consists of a robust steel construction with a material thickness of up to 2.0 mm. The cabinets are electrostatically powder-coated and available in the standard colours grey (RAL 7035) and black (RAL 9005). Modular lockable and removable side panels (horizontally divided from 42U) and doors improve accessibility. The door hinges can also be changed. The entire construction can be dismantled, meaning that the cabinets can be completely removed if required.

Remark: Picture similar

Technical specifications

Manufacturer ROLINE

Product group	19"-/10"-Cabinet
Product type	19"-Server cabinet
Colour	black
Scope of delivery	19-inch server enclosure 42 U, earthing cable set, installation kit for profile half cylinder, 2x spanners, installation set (screws, cage nuts, washers), assembly instructions
Height units	42 U
Minimum rack depth supported	675 mm
Maximum rack depth supported	875 mm
delivery condition	fully assembled
Material group	Steel
Server cabinet	yes
Wall mountable	no
Adjustable feet	yes
Maximum weight capacity	1000 kg
Protection class (IP Code)	IP20
Soundproof	no
Front	Steel door with perforation
Rack rails	yes
Side panels included	yes
Removeable side panels	yes
Removable front door	yes
Removable back door	yes
Ventilation	Passive
RAL colour	RAL 9005 Jet black
Height	1970 mm
Width	600 mm

Depth 1000 mm

Weight 103 kg