

Pneumatic spiral hose

Made of polyamide



Application:

For connection to compressed-air tools and compressed-air machines.

Execution:

- With special fitting connections at both ends
- Suitable for water and air
- Max. pressure: 10 bar
- Max. temperature: 90°C
- For a clearly organised workplace
- For reducing the risk of accidents



Art. no.	75052 030
Brand	PREVOST
Manufacturer Part Number	SPIC 65
Hose length	5 m
Outer diameter of hose	8 mm
Inner hose diameter	6 mm
Connection thread	G 1/4 inch
Max. operating pressure	10 bar
Gross Weight	0.284 kg
Product Group	758

EAN

3660058027939