

MODEL SMP-800A
MODEL SMP-1000A
MODEL SMP-2000A

**SWITCHING MODE
 UNIVERSAL REGULATED
 POWER SUPPLY**



**SMP-800A/
 SMP-1000A/
 SMP-2000A**

Features:

- Universal input voltage: 100-240V AC 50/60Hz
- Compact size and light.
- Stabilized output, low ripple.
- Short circuit & overload protection.
- High efficiency and low energy consumption.
- Power LED monitor.
- Uses with typewriters, personal computers, Cassette players, CD/MD players, Mini TV, TV games and other battery operated appliances.
- Especially uses with digital camera, multimedia, information technology(IT) equipment & computer accessories, etc.

MODEL	MAX. CURRENT	DC OUTPUT
SMP-800A	800mA	3 / 4.5 / 5 / 6 / 9 / 12V
SMP-1000A	1000mA	3 / 4.5 / 5 / 6 / 9 / 12V
SMP-2000A	2500mA	3 / 4.5 / 5 V
	2000mA	6 / 6.5 V
	1900mA	7 V

- Packing : Each in a clamshell pack.
- Export packing : 12pcs per inner box,
48pcs per export carton.



MEASUREMENT			N.W.	G.W.	QTY IN 20FT CONTAINER
50.5 X 42.5 X 39.5CM	0.085CBM	3.0CU.FT.	9.60KG	11.60KG	15840PCS

**SWITCHING MODE
 SINGLE OUTPUT REGULATED ADAPTOR**

MODEL	MAX. CURRENT	DC OUTPUT
SMP-1000A003	1000mA	3V DC
SMP-1000A4.5	1000mA	4.5V DC
SMP-1000A005	1000mA	5V DC
SMP-1000A006	1000mA	6V DC
SMP-1000A009	1000mA	9V DC
SMP-1000A012	1000mA	12V DC
SMP-2000A003	2500mA	3V DC
SMP-2000A4.5	2500mA	4.5V DC
SMP-2000A005	2500mA	5V DC
SMP-2000A006	2000mA	6V DC
SMP-2000A6.5	2000mA	6.5V DC
SMP-2000A007	1900mA	7V DC

- Packing : Each in a box.
- Export packing : 50pcs per inner box,
100pcs per export carton.

MEASUREMENT: 42.0x27.5x46.0cm (0.053CBM)

INPUT PLUG:

CODE:	(S) FOR EUROPEAN TYPE	(A) FOR AUSTRALIAN TYPE	(UK) FOR UK TYPE	(F) FOR AMERICAN TYPE
Dimension: mm				



119 gram only

