




LTR	REV.	DESCRIPTION	DATE
-----	------	-------------	------



DWG	P/N	L (mm)	T (mm)	PCS / CTN	CUFT	ZIP BAG SIZE	BAR CODE	CARTON SIZE (LxWxH mm)	LABEL
200-1145-3	119325	5000	50	40	1.66	B	4015867150528	410x410x280	LABEL 3
200-1145-2	119323	3000	30	50	1.26	B	4015867150511	381x302x311	LABEL 2
200-1145-1	119322	2000	30	80	1.46	B	4015867150504	460x300x300	LABEL 1

- NOTE:
- CABLE: UL-20276 [28AWG(7/0.127 T.C)×1P INS:FOAM-SKIN-PE+D.W(7/0.127 T.C)+Free-Edge-Foil/Mylar]×4C +28AWG(7/0.127 T.C)×1P INS:HD-PE+28AWG(7/0.127 T.C)×5C INS:HD-PE+AL/MY+D.W+B.D (85%) PVC JACKET OD:6.6±0.19mm COLOR:BLACK(NK-K01),(C20276415-1)  
CABLE MUST PRINTED: 1.3 Ver.
  - CONNECTOR:  
P1: HDMI 19P MALE W/PCB CONTACT:G/F; GOLD PLATED SHELL.  
P2: DVI 18+1 DIGITAL MALE CONTACT:G/F,GOLD PLATED SHELL.
  - SHIELD: P1:INNER MOLD MUST BE WRAPPED COPPER 360° TO CONNECTOR SHELL & CABLE BRAID  
P2:COPPER FOIL 360° SOLDER TO CONNECTOR SHELL & CABLE BRAID .
  - HOOD:P1&P2:MOLDED TYPE,PVC 45P,COLOR:BLACK(NK-K01) .
  - ELECTRICAL TEST:  
(1)100% OPEN SHORT & MIS WIRE TEST.  
(2)CONTACT RESISTANCE 3 ohm Max .  
(3)INSULATION RESISTANCE 10M ohm Min .  
(4)HI-POT DC300V
  - PACKING:EACH PC / **equip** ZIP BAG + BAR CODE LABEL  
10 PCS / BIG POLYBAG.

Tolerance Inch M/M								
. X	.015					.30	HDMI 1.3b to DVI-D Single Link Cable, black HDMI 19p/Male -> DVI 18+1p/Male	
. XX	.010	.10						
. XXX	.005	.05						
Draw	FANNIE 02/05/09'							
Chek			Scale	NONE	Units	M/M	Third Angle Projection	
Engr			Dwg No.	200-1145	REV:	A	Sheet:	1/3