

Multi-function tool HSS 90°

For universal use up to 1300 N/mm²

ORION[®]

Application:

For centring, drilling, countersinking, chamfering and peripheral milling.

Execution:

- Spiral-fluted design with grinding relief

Advantage:

- Universal point geometry ensures a broad range of uses
- TiNAlOX coating for increased service life requirements



Art. no.	11022 030
Brand	ORION
Manufacturer Part Number	11022030
Angle of the tip	90 Degree
Cutting material	HSS
Surface	TiNAlOX
Tool holding device	HA parallel shank
Cutting edge diameter	3 mm
Shank diameter	3 mm
Cutting edge length	6 mm
Length	50 mm
f steel 700	0.04 mm/r
Gross Weight	0.008 kg
Product Group	1AO

EAN

4039247793136