





COMPARTMENT STORAGE BOX PSK55000-PA1-4

- For safe marking of still-to-connect wires.
- 49-compartment storage box in impact-resistant plastic for convenient on-site combination marking.
- Perfect overview allows quick marking on mounting site.
- Transparent lid for visual confirmation of contents.
- Filled with PA1 markers and installation tools.

INFORMATION

Design

A compartment storage box with 49 removable compartments containing PA2 markers and installation

The PA1 marker is a closed and adjustable marker sleeve for wires still not connected. Its unique profile with spring-action collars covers a wide diameter range.

Material

PA1: Soft PVC

Characters

PA1: The characters are hot stamped for excellent readability and long-lasting durability.

Refills

Available from the standard Partex product range

Temperature range

PA1: Shape-resistant from -30 °C to +60 °C

PA1 durability

- Flame-proof UL94-V0 @ 3 mm.
- Chemical resistance meeting Partex' testing program.
- Temperature and aging resistance meeting Partex' testing program.

OVERVIEW

MARKER BOX CONTENTS

Product	Colour	Number/Product
A-Z	Yellow/Black	200
0-9	Yellow/Black	200
-/	Yellow/Black	200
GRD	Yellow-Green/Black	200
+	Red/White	200
-	Blue/White	200
Blank	Yellow	200
L1, L2, L3	Yellow/Black	100
N	Blue/White	200
Teflon-coated installation tool in stainless steel	-	2

Α	В	С	D	Ε	F	G	н	ı	J
К	L	М	N	0	Р	Q	R	s	Т
U	v	w	x	Y	Z	-	/	GRD	N
0	1	2	3	4	5	6	7	8	J5T
9	L1	L2	L3	-	+	BLANK	EMPTY	EMPTY	PADST

Placement in PSK55000-PA1 compartment storage box.

PRODUCT SIZES


Marker Box	Length, mm	Width, mm	Height, mm
PSK55000-PA1-4	410	320	50


Marker	Diameter mm	Area mm²	Inch	AWG
PA-1	2.5-5.0	~1.5-4.0	.099"197"	16-11

Installation tool	Length mm	Diameter mm	Inner diameter mm
PAD-5T	100	5,0	2,5

ACCESSORIES

PAD INSTALLATION TOOL





PAD-5T
Teflon-coated installation tool in stainless steel with axial hole at heavy end designed for wire fitting. PAD is designed for Partex PA02 and PA1 markers.

ORDERS

BESTÄLLNINGSINFORMATION OCH FÖRPACKNING

Article number	Description	Number/package
PA-10003AV40.A	PA YELLOW: A	200x5
PA-10003AV40.B	PA YELLOW: B	200x5
PA-10003AV40.C	PA YELLOW: C	200x5
PA-10003AV40.D	PA YELLOW: D	200x5
PA-10003AV40.E	PA YELLOW: E	200x5
PA-10003AV40.F	PA YELLOW: F	200x5
PA-10003AV40.G	PA YELLOW: G	200x5
PA-10003AV40.H	PA YELLOW: H	200x5
PA-10003AV40.I	PA YELLOW: I	200x5
PA-10003AV40.J	PA YELLOW: J	200x5
PA-10003AV40.K	PA YELLOW: K	200x5
PA-10003AV40.L	PA YELLOW: L	200x5
PA-10003AV40.M	PA YELLOW: M	200x5
PA-10003AV40.N	PA YELLOW: N	200x5
PA-10003AV40.O	PA YELLOW: O	200x5
PA-10003AV40.P	PA YELLOW: P	200x5
PA-10003AV40.Q	PA YELLOW: Q	200x5
PA-10003AV40.R	PA YELLOW: R	200x5
PA-10003AV40.S	PA YELLOW: S	200x5
PA-10003AV40.T	PA YELLOW: T	200x5
PA-10003AV40.U	PA YELLOW: U	200x5
PA-10003AV40.V	PA YELLOW: V	200x5
PA-10003AV40.W	PA YELLOW: W	200x5
PA-10003AV40.X	PA YELLOW: X	200x5
PA-10003AV40.Y	PA YELLOW: Y	200x5
PA-10003AV40.Z	PA YELLOW: Z	200x5
PA-10003AV40	PA YELLOW: -	200x5
PA-10003AV40./	PA YELLOW: /	200x5
PA-10003AV40.GRD	PA YELLOW-GREEN: GROUND	200x5
PA-10003AV69.N	PA BLUE: N	200x5
PA-10003AV40.0	PA YELLOW: 0	200x5
PA-10003AV40.1	PA YELLOW: 1	200x5
PA-10003AV40.2	PA YELLOW: 2	200x5
PA-10003AV40.3	PA YELLOW: 3	200x5
PA-10003AV40.4	PA YELLOW: 4	200x5
PA-10003AV40.5	PA YELLOW: 5	200x5
PA-10003AV40.6	PA YELLOW: 6	200x5
PA-10003AV40.7	PA YELLOW: 7	200x5
PA-10003AV40.8	PA YELLOW: 8	200x5
PA-10003AV40.9	PA YELLOW: 9	200x5
PA-10006AV40.L1	PA YELLOW: L1	100x5
PA-10006AV40.L2	PA YELLOW: L2	100x5
PA-10006AV40.L3	PA YELLOW: L3	100x5
PA-10003AV69	PA BLUE: -	200x5
PA-10003AV29.+	PA RED: +	200x5
PA-10003AN4	PA UNMARKED YELLOW	200x5
PAD-5T	PAD 5 TEFLON-COATED	1
	INSTALLATION TOOL	