

Electronic dial gauge

ID-U

Mitutoyo

Application:

For measuring, e.g. in devices on production machines

Execution:

- ABSOLUTE system for reliable measurement
- ON/OFF
- LCD digit size 8.5 mm
- Digimatic
- Counting direction can be switched
- Narrow construction with 25 mm measuring range

Advantage:

- Long battery life



Art. no.	32019 312
Brand	MITUTOYO
Manufacturer Part Number	575-123
Length measuring range	25.4 mm
Digit increment	0.01 mm
Max. length measuring range in inches	1 in
Digit increment in inches	0.0005 in
Min./max. measurement force	0-1.5 N
Error limit	0.02 mm
Data transmission type	DIGIMATIC
Functions	ABS function, Origin (Dimension preset), Reversal of counting direction, With mm / inch switching
Absolute function	Yes
Automatic switch-off	No
Dynamic measurement	No
Preset function	No
Shank diameter	9.52 mm
Tolerance value entry	No
Manual tolerance markers	No
Number of rechargeable batteries/batteries	1 PCS
Colour reading classification	No
Rechargeable battery/battery capacity	155 mAh
Battery voltage	1.55 V
Weight of rechargeable battery/battery	0.002 kg
Battery designation	1,5 V SR44
Rotating housing	No
Combined indicator for figure/scale reading	No
Reversible counting direction	Yes
Digit height	8.5 mm
Design	Metric, Imperial
Display	Digital
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	0.270 kg
Product Group	3MA

EAN

4946368131290